

Product group: 196 Product number: 633230

Filter glasses for arc welding

Product information



For use up to 20 Amp, the glasses have dimensions 60 x110 mm and are manufactured in accordance with DIN standard and are CE approved. When ordering face shields, filter shade glass of correct shade should be ordered in addition to the filter shade 11 glasses which are included. The filter glasses are supplied in sets consisting of 5 safety glasses, 5 protection glasses and 5 filter shade glasses.

Specification

General

Invent Hazard Material (IMO/EJ) classification NA

Approvals

CE

Documents

SDoC and MD for IHM

Directions for use

A Safety glass (polycarbonate)

The glass is used in shields with a flip-up front frame and should be placed nearest to the eyes to protect against slag or other articles while chipping/ grinding when the flip up front is open.

B. Filter shade glass

Filters out harmful infra-red and ultra-violet rays from the welding arc, and reduces visible light to a level which is sufficient to see the welding process without straining the welder's eyes. Filter Shade Glass should be selected based on welding process and amperage. The glasses are marked Protane Shade SO 1 DIN 0196 CE

C. Protection glass

The glass is placed in front of the filter shade glass to protect gainst spatter. The protection glass should be replaced at regular intervals.

Related products

Is accessory to 709485 FLIPVISION WELDING FACE SHIELD 619098 FACE SHIELD W/HANDLE 619114 SAFETY HELMW/FACE SH.

Is frequently bought together with

699165 GPO-302N 2.5X350MM 295 PCS 5,2KG 633248 SHADE 9 GLASS. 5SET 699173 GPO-302N 3.2X350MM 190 PCS 5.4 KG 633255 SHADE 10 GLASS. 5SET 632786 WELDERS GLOVES. 6 PAIRS This page is printed from:

https://www.wilhelmsen.com/product-catalogue/products/welding/arc-welding-equipment/welders-protection/shade-8-glass.-5set the set of the set